

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207716

Luminaire Tested: **LD4B50D010TE EU4B30509727 4LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207716
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509727 4LBNH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2320.9 lumens
Efficiency: N/A
Efficacy: 39.5 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207716

CATALOG NUMBER: LD4B50D010TE EU4B30509727 4LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P207716

CATALOG NUMBER: LD4B50D010TE EU4B30509727 4LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207716

CATALOG NUMBER: LD4B50D010TE EU4B30509727 4LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	262.9	11.3
10°-20°	637.8	27.5
20°-30°	740.4	31.9
30°-40°	490.3	21.1
40°-50°	137.5	5.9
50°-60°	34.6	1.5
60°-70°	12.9	0.6
70°-80°	4.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1641.1	70.7
0°-40°	2131.5	91.8
0°-60°	2303.5	99.3
0°-90°	2320.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2320.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2914	
5°	2838	263
15°	2283	638
25°	1623	740
35°	786	490
45°	160	138
55°	38	35
65°	13	13
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P207716

CATALOG NUMBER: LD4B50D010TE EU4B30509727 4LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2914.0
2.5°	2901.4
5°	2838.3
7.5°	2729.0
10°	2594.4
12.5°	2443.1
15°	2283.3
17.5°	2127.7
20°	1955.3
22.5°	1795.5
25°	1623.1
27.5°	1459.1
30°	1248.9
32.5°	1026.0
35°	786.3
37.5°	563.5
40°	382.6
42.5°	248.1
45°	159.8
47.5°	96.7
50°	63.1
52.5°	46.3
55°	37.8
57.5°	29.4
60°	21.0
62.5°	16.8
65°	12.6
67.5°	8.4
70°	8.4
72.5°	4.2
75°	4.2
77.5°	4.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)