

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839251

Luminaire Tested: **LD4C30D010 EU4309027 4LBPSMW**

Issue Date: 6/29/2023

Test Information

Test Method: LM-79-08
Report Number: P839251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30D010 EU4309027 4LBPSMW
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBPS TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2773.0 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839251

CATALOG NUMBER: LD4C30D010 EU4309027 4LBPSMW

Luminous Intensity Polar Plot





TEST NUMBER: P839251

CATALOG NUMBER: LD4C30D010 EU4309027 4LBPSMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159771
5°	159518
10°	158643
15°	156809
20°	153957
25°	150627
30°	147037
35°	142853
40°	137104
45°	127178
50°	109553
55°	87389
60°	68036
65°	50930
70°	36962
75°	29287
80°	27450
85°	27346



TEST NUMBER: P839251

CATALOG NUMBER: LD4C30D010 EU4309027 4LBPSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.8	4.4
10°-20°	347.2	12.5
20°-30°	511.7	18.5
30°-40°	594.4	21.4
40°-50°	558.7	20.1
50°-60°	369.8	13.3
60°-70°	178.2	6.4
70°-80°	68.7	2.5
80°-90°	21.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	981.7	35.4
0°-40°	1576.1	56.8
0°-60°	2504.6	90.3
0°-90°	2773.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2773.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1300	
5°	1294	123
15°	1233	347
25°	1111	512
35°	952	594
45°	732	559
55°	408	370
65°	175	178
75°	62	69
85°	19	21
90°	0	



TEST NUMBER: P839251

CATALOG NUMBER: LD4C30D010 EU4309027 4LBPSMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1300.5
2.5°	1299.3
5°	1293.5
7.5°	1284.6
10°	1271.7
12.5°	1254.1
15°	1232.9
17.5°	1207.0
20°	1177.6
22.5°	1145.3
25°	1111.2
27.5°	1074.7
30°	1036.5
32.5°	996.0
35°	952.5
37.5°	904.8
40°	854.9
42.5°	798.4
45°	732.0
47.5°	656.7
50°	573.2
52.5°	488.6
55°	408.0
57.5°	338.6
60°	276.9
62.5°	221.7
65°	175.2
67.5°	135.8
70°	102.9
72.5°	78.2
75°	61.7
77.5°	50.0
80°	38.8
82.5°	28.8
85°	19.4
87.5°	11.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)