

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252038

Luminaire Tested: **LD4B50D010TE EU4B30508030 4LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-3)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508030 4LBBA1MW
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6225.0 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.99
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252038

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252038

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88				88
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78				78
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69				69
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62				62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56				56
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51				51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46				46
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43				43
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39				39
10	62	50	43	39	61	50	43	38	49	43	38	48	42	38	47	42	38	37				37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	424274
5°	419927
10°	407316
15°	390972
20°	373387
25°	349192
30°	303957
35°	234546
40°	173544
45°	136559
50°	117292
55°	106654
60°	97224
65°	89982
70°	83148
75°	77946
80°	72344
85°	68322



TEST NUMBER: P252038

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	404.0	6.5
10°-20°	1089.0	17.5
20°-30°	1473.6	23.7
30°-40°	1238.2	19.9
40°-50°	783.5	12.6
50°-60°	562.7	9.0
60°-70°	387.3	6.2
70°-80°	219.2	3.5
80°-90°	67.4	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2966.6	47.7
0°-40°	4204.8	67.5
0°-60°	5551.1	89.2
0°-90°	6225.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6225.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4353	
5°	4292	404
15°	3875	1089
25°	3247	1474
35°	1971	1238
45°	991	784
55°	628	563
65°	390	387
75°	207	219
85°	61	67
90°	0	



TEST NUMBER: P252038

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBBA1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4353.4
2.5°	4339.9
5°	4292.4
7.5°	4214.3
10°	4115.9
12.5°	4000.6
15°	3875.0
17.5°	3739.3
20°	3600.2
22.5°	3437.3
25°	3247.3
27.5°	3003.0
30°	2701.0
32.5°	2348.1
35°	1971.4
37.5°	1638.9
40°	1364.1
42.5°	1150.3
45°	990.8
47.5°	868.7
50°	773.6
52.5°	695.6
55°	627.7
57.5°	559.9
60°	498.8
62.5°	441.1
65°	390.2
67.5°	339.3
70°	291.8
72.5°	247.7
75°	207.0
77.5°	166.3
80°	128.9
82.5°	95.0
85°	61.1
87.5°	27.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)