

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839272

Luminaire Tested: **LD4C35D010 EU4359035 4LBPSMW**

Issue Date: 6/29/2023

Test Information

Test Method: LM-79-08
Report Number: P839272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35D010 EU4359035 4LBPSMW
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBPS TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3450.0 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839272

CATALOG NUMBER: LD4C35D010 EU4359035 4LBPSMW

Luminous Intensity Polar Plot





TEST NUMBER: P839272

CATALOG NUMBER: LD4C35D010 EU4359035 4LBPSMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	198777
5°	198451
10°	197377
15°	195093
20°	191544
25°	187403
30°	182941
35°	177722
40°	170574
45°	158226
50°	136311
55°	108722
60°	84646
65°	63372
70°	45978
75°	36455
80°	34172
85°	33971



TEST NUMBER: P839272

CATALOG NUMBER: LD4C35D010 EU4359035 4LBPSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.8	4.4
10°-20°	432.0	12.5
20°-30°	636.6	18.5
30°-40°	739.5	21.4
40°-50°	695.1	20.1
50°-60°	460.1	13.3
60°-70°	221.7	6.4
70°-80°	85.5	2.5
80°-90°	26.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1221.3	35.4
0°-40°	1960.8	56.8
0°-60°	3116.1	90.3
0°-90°	3450.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3450.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1618	
5°	1609	153
15°	1534	432
25°	1382	637
35°	1185	740
45°	911	695
55°	508	460
65°	218	222
75°	77	86
85°	24	27
90°	0	



TEST NUMBER: P839272

CATALOG NUMBER: LD4C35D010 EU4359035 4LBPSMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1618.0
2.5°	1616.5
5°	1609.2
7.5°	1598.3
10°	1582.2
12.5°	1560.2
15°	1533.9
17.5°	1501.7
20°	1465.1
22.5°	1424.9
25°	1382.5
27.5°	1337.1
30°	1289.6
32.5°	1239.1
35°	1185.0
37.5°	1125.7
40°	1063.6
42.5°	993.3
45°	910.7
47.5°	817.1
50°	713.2
52.5°	607.9
55°	507.6
57.5°	421.3
60°	344.5
62.5°	275.8
65°	218.0
67.5°	169.0
70°	128.0
72.5°	97.3
75°	76.8
77.5°	62.2
80°	48.3
82.5°	35.8
85°	24.1
87.5°	13.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)