

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206367

Luminaire Tested: **LD4B50D010TE EU4B30508030 4LBCEMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206367  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30508030 4LBCSMW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5425.1 lumens  
Efficiency: N/A  
Efficacy: 92.3 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206367

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P206367

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBCSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206367

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.9	3.9
10°-20°	597.7	11.0
20°-30°	899.1	16.6
30°-40°	1065.5	19.6
40°-50°	1060.4	19.5
50°-60°	854.8	15.8
60°-70°	517.1	9.5
70°-80°	192.0	3.5
80°-90°	28.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1706.7	31.5
0°-40°	2772.2	51.1
0°-60°	4687.4	86.4
0°-90°	5425.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5425.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2216	
5°	2206	210
15°	2117	598
25°	1953	899
35°	1706	1066
45°	1381	1060
55°	953	855
65°	519	517
75°	174	192
85°	23	29
90°	0	



TEST NUMBER: P206367

CATALOG NUMBER: LD4B50D010TE EU4B30508030 4LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2215.8
2.5°	2215.8
5°	2205.9
7.5°	2199.4
10°	2179.6
12.5°	2146.8
15°	2117.2
17.5°	2084.3
20°	2044.8
22.5°	2005.4
25°	1952.8
27.5°	1896.9
30°	1834.4
32.5°	1775.3
35°	1706.2
37.5°	1633.9
40°	1548.4
42.5°	1466.2
45°	1380.8
47.5°	1285.4
50°	1180.2
52.5°	1071.7
55°	953.4
57.5°	848.2
60°	729.8
62.5°	624.6
65°	519.4
67.5°	420.8
70°	328.8
72.5°	246.6
75°	174.2
77.5°	111.8
80°	65.8
82.5°	39.5
85°	23.0
87.5°	9.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)