

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839283

Luminaire Tested: **LD4C40D010 EU4409027 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P839283
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C40D010 EU4409027 4LBSLI
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3965.0 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839283
CATALOG NUMBER: LD4C40D010 EU4409027 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839283

CATALOG NUMBER: LD4C40D010 EU4409027 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	347810
5°	339939
10°	319232
15°	296995
20°	275452
25°	251086
30°	223541
35°	198149
40°	178095
45°	159390
50°	136732
55°	110007
60°	81968
65°	52325
70°	25216
75°	4177
80°	3113
85°	0



TEST NUMBER: P839283

CATALOG NUMBER: LD4C40D010 EU4409027 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.7	6.5
10°-20°	654.7	16.5
20°-30°	848.4	21.4
30°-40°	831.3	21.0
40°-50°	704.6	17.8
50°-60°	461.9	11.6
60°-70°	185.7	4.7
70°-80°	21.2	0.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1759.8	44.4
0°-40°	2591.1	65.3
0°-60°	3757.5	94.8
0°-90°	3965.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3965.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2831	
5°	2756	257
15°	2335	655
25°	1852	848
35°	1321	831
45°	917	705
55°	514	462
65°	180	186
75°	9	21
85°	0	1
90°	0	



TEST NUMBER: P839283

CATALOG NUMBER: LD4C40D010 EU4409027 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2831.1
2.5°	2809.2
5°	2756.5
7.5°	2668.7
10°	2559.0
12.5°	2440.5
15°	2335.1
17.5°	2221.1
20°	2106.9
22.5°	1984.0
25°	1852.3
27.5°	1716.2
30°	1575.8
32.5°	1444.1
35°	1321.2
37.5°	1220.3
40°	1110.5
42.5°	1013.9
45°	917.4
47.5°	816.4
50°	715.4
52.5°	614.5
55°	513.6
57.5°	421.4
60°	333.6
62.5°	254.6
65°	180.0
67.5°	118.5
70°	70.2
72.5°	30.7
75°	8.8
77.5°	4.4
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)