

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206373

Luminaire Tested: **LD4B50D010TE EU4B30509030 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509030 4LBCSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4633.2 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206373

CATALOG NUMBER: LD4B50D010TE EU4B30509030 4LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206373

CATALOG NUMBER: LD4B50D010TE EU4B30509030 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87				87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74				74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63				63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55				55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48				48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42				42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37				37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33				33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30				30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206373

CATALOG NUMBER: LD4B50D010TE EU4B30509030 4LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.3	3.9
10°-20°	510.4	11.0
20°-30°	767.8	16.6
30°-40°	910.0	19.6
40°-50°	905.6	19.5
50°-60°	730.0	15.8
60°-70°	441.6	9.5
70°-80°	164.0	3.5
80°-90°	24.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1457.6	31.5
0°-40°	2367.5	51.1
0°-60°	4003.2	86.4
0°-90°	4633.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4633.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1892	
5°	1884	179
15°	1808	510
25°	1668	768
35°	1457	910
45°	1179	906
55°	814	730
65°	444	442
75°	149	164
85°	20	24
90°	0	



TEST NUMBER: P206373

CATALOG NUMBER: LD4B50D010TE EU4B30509030 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1892.3
2.5°	1892.3
5°	1883.9
7.5°	1878.3
10°	1861.5
12.5°	1833.4
15°	1808.1
17.5°	1780.0
20°	1746.3
22.5°	1712.6
25°	1667.7
27.5°	1620.0
30°	1566.7
32.5°	1516.1
35°	1457.2
37.5°	1395.4
40°	1322.4
42.5°	1252.2
45°	1179.2
47.5°	1097.8
50°	1007.9
52.5°	915.3
55°	814.2
57.5°	724.4
60°	623.3
62.5°	533.4
65°	443.6
67.5°	359.4
70°	280.8
72.5°	210.6
75°	148.8
77.5°	95.5
80°	56.2
82.5°	33.7
85°	19.7
87.5°	8.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)