

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205645

Luminaire Tested: **LD4B50D010TE EU4B30509030 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205645
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509030 4LBSWMH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4421.2 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205645

CATALOG NUMBER: LD4B50D010TE EU4B30509030 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P205645

CATALOG NUMBER: LD4B50D010TE EU4B30509030 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205645

CATALOG NUMBER: LD4B50D010TE EU4B30509030 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.0	5.9
10°-20°	686.3	15.5
20°-30°	921.7	20.8
30°-40°	943.5	21.3
40°-50°	816.7	18.5
50°-60°	543.2	12.3
60°-70°	223.1	5.0
70°-80°	26.5	0.6
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1867.1	42.2
0°-40°	2810.5	63.6
0°-60°	4170.4	94.3
0°-90°	4421.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4421.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2802	
5°	2759	259
15°	2452	686
25°	2011	922
35°	1507	943
45°	1064	817
55°	603	543
65°	220	223
75°	12	27
85°	0	1
90°	0	



TEST NUMBER: P205645

CATALOG NUMBER: LD4B50D010TE EU4B30509030 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2802.1
2.5°	2796.3
5°	2758.7
7.5°	2700.7
10°	2622.5
12.5°	2535.5
15°	2451.5
17.5°	2344.3
20°	2240.0
22.5°	2129.9
25°	2011.1
27.5°	1883.5
30°	1756.0
32.5°	1628.5
35°	1506.8
37.5°	1390.9
40°	1280.8
42.5°	1170.7
45°	1063.5
47.5°	950.5
50°	834.6
52.5°	718.6
55°	602.7
57.5°	501.3
60°	397.0
62.5°	301.4
65°	220.2
67.5°	144.9
70°	84.0
72.5°	40.6
75°	11.6
77.5°	5.8
80°	2.9
82.5°	2.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)