

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207305

Luminaire Tested: **LD4B50D010TE EU4B30509730 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509730 4LBMWH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2980.3 lumens
Efficiency: N/A
Efficacy: 50.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207305

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P207305

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71			
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66			
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62			
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207305

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	327.0	11.0
10°-20°	840.7	28.2
20°-30°	986.3	33.1
30°-40°	624.2	20.9
40°-50°	167.2	5.6
50°-60°	23.4	0.8
60°-70°	8.7	0.3
70°-80°	2.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2154.0	72.3
0°-40°	2778.2	93.2
0°-60°	2968.8	99.6
0°-90°	2980.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2980.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3540	
5°	3482	327
15°	3011	841
25°	2179	986
35°	991	624
45°	189	167
55°	22	23
65°	9	9
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P207305

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	3539.6
2.5°	3526.4
5°	3482.3
7.5°	3411.9
10°	3310.6
12.5°	3178.6
15°	3011.3
17.5°	2839.6
20°	2632.7
22.5°	2421.3
25°	2179.2
27.5°	1915.1
30°	1620.1
32.5°	1298.7
35°	990.6
37.5°	717.6
40°	493.1
42.5°	317.0
45°	189.3
47.5°	105.7
50°	57.2
52.5°	30.8
55°	22.0
57.5°	17.6
60°	13.2
62.5°	13.2
65°	8.8
67.5°	4.4
70°	4.4
72.5°	4.4
75°	4.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)