

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207820

Luminaire Tested: **LD4B50D010TE EU4B30509730 4LBNGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207820  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30509730 4LBNGPH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1818.1 lumens  
Efficiency: N/A  
Efficacy: 30.9 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207820

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBNGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207820

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBNGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207820

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBNGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	198.2	10.9
10°-20°	496.9	27.3
20°-30°	605.6	33.3
30°-40°	399.6	22.0
40°-50°	92.0	5.1
50°-60°	17.6	1.0
60°-70°	6.5	0.4
70°-80°	1.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1300.7	71.5
0°-40°	1700.3	93.5
0°-60°	1809.9	99.5
0°-90°	1818.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1818.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2180	
5°	2128	198
15°	1780	497
25°	1330	606
35°	639	400
45°	101	92
55°	18	18
65°	4	6
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P207820

CATALOG NUMBER: LD4B50D010TE EU4B30509730 4LBNGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2180.3
2.5°	2175.9
5°	2127.5
7.5°	2061.4
10°	1973.3
12.5°	1885.2
15°	1779.5
17.5°	1669.4
20°	1554.8
22.5°	1453.5
25°	1330.2
27.5°	1206.9
30°	1048.3
32.5°	854.5
35°	638.7
37.5°	444.9
40°	286.3
42.5°	176.2
45°	101.3
47.5°	52.9
50°	30.8
52.5°	26.4
55°	17.6
57.5°	13.2
60°	13.2
62.5°	8.8
65°	4.4
67.5°	4.4
70°	4.4
72.5°	4.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)