

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839331

Luminaire Tested: **LD4C55D010 EU4559030 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P839331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C55D010 EU4559030 4LBSLI
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6043.0 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839331

CATALOG NUMBER: LD4C55D010 EU4559030 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839331

CATALOG NUMBER: LD4C55D010 EU4559030 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	530100
5°	518091
10°	486532
15°	452647
20°	419813
25°	382682
30°	340703
35°	301992
40°	271433
45°	242925
50°	208404
55°	167645
60°	124917
65°	79738
70°	38434
75°	6361
80°	4669
85°	0



TEST NUMBER: P839331

CATALOG NUMBER: LD4C55D010 EU4559030 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.3	6.5
10°-20°	997.8	16.5
20°-30°	1293.0	21.4
30°-40°	1266.9	21.0
40°-50°	1073.8	17.8
50°-60°	703.9	11.6
60°-70°	282.9	4.7
70°-80°	32.3	0.5
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2682.1	44.4
0°-40°	3949.0	65.3
0°-60°	5726.8	94.8
0°-90°	6043.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6043.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4315	
5°	4201	391
15°	3559	998
25°	2823	1293
35°	2014	1267
45°	1398	1074
55°	783	704
65°	274	283
75°	13	32
85°	0	1
90°	0	



TEST NUMBER: P839331

CATALOG NUMBER: LD4C55D010 EU4559030 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4314.9
2.5°	4281.4
5°	4201.1
7.5°	4067.3
10°	3900.1
12.5°	3719.5
15°	3558.9
17.5°	3385.1
20°	3211.1
22.5°	3023.8
25°	2823.1
27.5°	2615.7
30°	2401.7
32.5°	2201.0
35°	2013.6
37.5°	1859.8
40°	1692.5
42.5°	1545.3
45°	1398.2
47.5°	1244.3
50°	1090.4
52.5°	936.6
55°	782.7
57.5°	642.2
60°	508.4
62.5°	388.0
65°	274.3
67.5°	180.6
70°	107.0
72.5°	46.8
75°	13.4
77.5°	6.6
80°	6.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)