

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839344

Luminaire Tested: **LD4C60D010 EU4609030 4LBPSMW**

Issue Date: 6/29/2023

Test Information

Test Method: LM-79-08
Report Number: P839344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C60D010 EU4609030 4LBPSMW
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBPS TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6258.0 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839344

CATALOG NUMBER: LD4C60D010 EU4609030 4LBPSMW

Luminous Intensity Polar Plot





TEST NUMBER: P839344

CATALOG NUMBER: LD4C60D010 EU4609030 4LBPSMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	360563
5°	359979
10°	358016
15°	353873
20°	347449
25°	339928
30°	331837
35°	322374
40°	309393
45°	287003
50°	247260
55°	197225
60°	153542
65°	114941
70°	83406
75°	66121
80°	61976
85°	61740



TEST NUMBER: P839344

CATALOG NUMBER: LD4C60D010 EU4609030 4LBPSMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.1	4.4
10°-20°	783.6	12.5
20°-30°	1154.7	18.5
30°-40°	1341.4	21.4
40°-50°	1260.9	20.1
50°-60°	834.6	13.3
60°-70°	402.2	6.4
70°-80°	155.1	2.5
80°-90°	48.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2215.4	35.4
0°-40°	3556.8	56.8
0°-60°	5652.4	90.3
0°-90°	6258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6258.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2935	
5°	2919	277
15°	2782	784
25°	2508	1155
35°	2150	1341
45°	1652	1261
55°	921	835
65°	395	402
75°	139	155
85°	44	48
90°	0	



TEST NUMBER: P839344

CATALOG NUMBER: LD4C60D010 EU4609030 4LBPSMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2934.9
2.5°	2932.3
5°	2919.0
7.5°	2899.1
10°	2869.9
12.5°	2830.1
15°	2782.3
17.5°	2724.0
20°	2657.6
22.5°	2584.7
25°	2507.7
27.5°	2425.4
30°	2339.2
32.5°	2247.6
35°	2149.5
37.5°	2042.0
40°	1929.2
42.5°	1801.8
45°	1651.9
47.5°	1482.1
50°	1293.7
52.5°	1102.6
55°	920.8
57.5°	764.3
60°	624.9
62.5°	500.2
65°	395.4
67.5°	306.5
70°	232.2
72.5°	176.5
75°	139.3
77.5°	112.8
80°	87.6
82.5°	65.0
85°	43.8
87.5°	25.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)