

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839348

Luminaire Tested: **LD4C60D010 EU4609035 4LBSH**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839348  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C60D010 EU4609035 4LBSH  
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6352.0 lumens  
Efficiency: N/A  
Efficacy: 88.2 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839348

CATALOG NUMBER: LD4C60D010 EU4609035 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P839348

CATALOG NUMBER: LD4C60D010 EU4609035 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	408119
5°	406237
10°	397849
15°	383393
20°	365739
25°	346028
30°	326403
35°	307332
40°	289379
45°	269750
50°	245960
55°	217230
60°	183863
65°	144360
70°	103018
75°	56438
80°	9976
85°	0



TEST NUMBER: P839348

CATALOG NUMBER: LD4C60D010 EU4609035 4LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	311.2	4.9
10°-20°	845.8	13.3
20°-30°	1174.6	18.5
30°-40°	1281.7	20.2
40°-50°	1195.7	18.8
50°-60°	907.5	14.3
60°-70°	496.9	7.8
70°-80°	136.8	2.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2331.5	36.7
0°-40°	3613.2	56.9
0°-60°	5716.4	90.0
0°-90°	6352.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6352.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3322	
5°	3294	311
15°	3014	846
25°	2553	1175
35°	2049	1282
45°	1553	1196
55°	1014	908
65°	497	497
75°	119	137
85°	0	2
90°	0	



TEST NUMBER: P839348

CATALOG NUMBER: LD4C60D010 EU4609035 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3322.0
2.5°	3322.0
5°	3294.1
7.5°	3252.2
10°	3189.2
12.5°	3105.4
15°	3014.4
17.5°	2902.6
20°	2797.5
22.5°	2671.6
25°	2552.7
27.5°	2433.9
30°	2300.9
32.5°	2175.1
35°	2049.2
37.5°	1923.3
40°	1804.4
42.5°	1678.5
45°	1552.6
47.5°	1426.7
50°	1286.9
52.5°	1153.9
55°	1014.2
57.5°	881.2
60°	748.3
62.5°	615.5
65°	496.6
67.5°	384.6
70°	286.8
72.5°	195.9
75°	118.9
77.5°	55.9
80°	14.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)