

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206883

Luminaire Tested: **LD4B50D010TE EU4B30508035 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206883
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508035 4LBWGPH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3489.9 lumens
Efficiency: N/A
Efficacy: 59.4 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206883

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBWGP1

Luminous Intensity Polar Plot





TEST NUMBER: P206883

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBWGP1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92				92
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76				76
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69				69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63				63
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57				57
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53				53
8	73	62	56	51	72	62	55	51	61	55	50	59	54	50	58	54	50	48				48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45				45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41				41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206883

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.9	6.8
10°-20°	671.5	19.2
20°-30°	962.9	27.6
30°-40°	906.7	26.0
40°-50°	500.7	14.3
50°-60°	160.6	4.6
60°-70°	40.2	1.2
70°-80°	9.6	0.3
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1871.3	53.6
0°-40°	2778.0	79.6
0°-60°	3439.3	98.6
0°-90°	3489.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3489.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2512	
5°	2500	237
15°	2379	671
25°	2112	963
35°	1471	907
45°	636	501
55°	163	161
65°	36	40
75°	6	10
85°	0	1
90°	0	



TEST NUMBER: P206883

CATALOG NUMBER: LD4B50D010TE EU4B30508035 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2511.8
2.5°	2493.7
5°	2499.7
7.5°	2481.5
10°	2451.3
12.5°	2421.0
15°	2378.7
17.5°	2342.3
20°	2281.8
22.5°	2197.1
25°	2112.3
27.5°	1997.3
30°	1846.0
32.5°	1676.6
35°	1470.8
37.5°	1252.9
40°	1028.9
42.5°	823.1
45°	635.5
47.5°	478.2
50°	345.0
52.5°	242.1
55°	163.4
57.5°	108.9
60°	78.7
62.5°	54.5
65°	36.3
67.5°	24.2
70°	18.2
72.5°	12.1
75°	6.1
77.5°	6.1
80°	6.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)