

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839369

Luminaire Tested: **LD4C65D010 EU4659050 4LBSH**

Issue Date: 2/14/2022

Test Information

Test Method: LM-79-08
Report Number: P839369
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C65D010 EU4659050 4LBSH
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6791.1 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839369

CATALOG NUMBER: LD4C65D010 EU4659050 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839369

CATALOG NUMBER: LD4C65D010 EU4659050 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	436326
5°	434318
10°	425343
15°	409886
20°	391024
25°	369940
30°	348973
35°	328568
40°	309377
45°	288393
50°	262970
55°	232245
60°	196590
65°	154331
70°	110166
75°	60378
80°	10612
85°	0



TEST NUMBER: P839369

CATALOG NUMBER: LD4C65D010 EU4659050 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.7	4.9
10°-20°	904.2	13.3
20°-30°	1255.7	18.5
30°-40°	1370.3	20.2
40°-50°	1278.3	18.8
50°-60°	970.3	14.3
60°-70°	531.3	7.8
70°-80°	146.2	2.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2492.7	36.7
0°-40°	3863.0	56.9
0°-60°	6111.5	90.0
0°-90°	6791.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6791.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3552	
5°	3522	333
15°	3223	904
25°	2729	1256
35°	2191	1370
45°	1660	1278
55°	1084	970
65°	531	531
75°	127	146
85°	0	2
90°	0	



TEST NUMBER: P839369

CATALOG NUMBER: LD4C65D010 EU4659050 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3551.6
2.5°	3551.6
5°	3521.8
7.5°	3477.0
10°	3409.6
12.5°	3320.0
15°	3222.7
17.5°	3103.2
20°	2990.9
22.5°	2856.3
25°	2729.1
27.5°	2602.1
30°	2460.0
32.5°	2325.4
35°	2190.8
37.5°	2056.2
40°	1929.1
42.5°	1794.5
45°	1659.9
47.5°	1525.3
50°	1375.9
52.5°	1233.7
55°	1084.3
57.5°	942.1
60°	800.1
62.5°	658.1
65°	530.9
67.5°	411.2
70°	306.7
72.5°	209.4
75°	127.2
77.5°	59.8
80°	15.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)