

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205750

Luminaire Tested: **LD4B50D010TE EU4B30509035 4LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509035 4LBSH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4423.3 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205750

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LB5H1

Luminous Intensity Polar Plot





TEST NUMBER: P205750

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205750

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.7	4.9
10°-20°	589.0	13.3
20°-30°	817.9	18.5
30°-40°	892.5	20.2
40°-50°	832.6	18.8
50°-60°	632.0	14.3
60°-70°	346.1	7.8
70°-80°	95.2	2.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1623.5	36.7
0°-40°	2516.1	56.9
0°-60°	3980.7	90.0
0°-90°	4423.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4423.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2313	
5°	2294	217
15°	2099	589
25°	1778	818
35°	1427	893
45°	1081	833
55°	706	632
65°	346	346
75°	83	95
85°	0	1
90°	0	



TEST NUMBER: P205750

CATALOG NUMBER: LD4B50D010TE EU4B30509035 4LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2313.4
2.5°	2313.4
5°	2293.9
7.5°	2264.7
10°	2220.8
12.5°	2162.4
15°	2099.1
17.5°	2021.1
20°	1948.1
22.5°	1860.4
25°	1777.6
27.5°	1694.8
30°	1602.3
32.5°	1514.6
35°	1427.0
37.5°	1339.3
40°	1256.5
42.5°	1168.9
45°	1081.2
47.5°	993.5
50°	896.1
52.5°	803.6
55°	706.2
57.5°	613.6
60°	521.1
62.5°	428.6
65°	345.8
67.5°	267.9
70°	199.7
72.5°	136.4
75°	82.8
77.5°	39.0
80°	9.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)