

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839386

Luminaire Tested: **LD4C75D010 EU4759027 4LBPSMW**

Issue Date: 6/29/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P839386  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/29/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C75D010 EU4759027 4LBPSMW  
Description: 4 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBPS TRIM WITH MW FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7775.0 lumens  
Efficiency: N/A  
Efficacy: 95.4 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 81.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839386

CATALOG NUMBER: LD4C75D010 EU4759027 4LBPSMW

### Luminous Intensity Polar Plot





TEST NUMBER: P839386

CATALOG NUMBER: LD4C75D010 EU4759027 4LBPSMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	447973
5°	447242
10°	444804
15°	439661
20°	431684
25°	422331
30°	412271
35°	400512
40°	384400
45°	356569
50°	307178
55°	245032
60°	190767
65°	142790
70°	103629
75°	82165
80°	76974
85°	76681



TEST NUMBER: P839386

CATALOG NUMBER: LD4C75D010 EU4759027 4LBPSMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	344.3	4.4
10°-20°	973.5	12.5
20°-30°	1434.6	18.5
30°-40°	1666.6	21.4
40°-50°	1566.5	20.1
50°-60°	1037.0	13.3
60°-70°	499.7	6.4
70°-80°	192.7	2.5
80°-90°	60.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2752.4	35.4
0°-40°	4419.0	56.8
0°-60°	7022.5	90.3
0°-90°	7775.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7775.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3646	
5°	3627	344
15°	3457	974
25°	3116	1435
35°	2670	1667
45°	2052	1567
55°	1144	1037
65°	491	500
75°	173	193
85°	54	60
90°	0	



TEST NUMBER: P839386

CATALOG NUMBER: LD4C75D010 EU4759027 4LBPSMW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3646.4
2.5°	3643.1
5°	3626.6
7.5°	3601.9
10°	3565.6
12.5°	3516.2
15°	3456.8
17.5°	3384.3
20°	3301.9
22.5°	3211.2
25°	3115.6
27.5°	3013.4
30°	2906.2
32.5°	2792.5
35°	2670.5
37.5°	2537.0
40°	2396.9
42.5°	2238.6
45°	2052.3
47.5°	1841.3
50°	1607.2
52.5°	1369.9
55°	1144.0
57.5°	949.5
60°	776.4
62.5°	621.5
65°	491.2
67.5°	380.8
70°	288.5
72.5°	219.2
75°	173.1
77.5°	140.1
80°	108.8
82.5°	80.8
85°	54.4
87.5°	31.3
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)