

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206884

Luminaire Tested: **LD4B50D010TE EU4B30508040 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206884
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508040 4LBWGPH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3524.6 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206884

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P206884

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBWGP1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	99	100	98	96	96	95	94	92			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	77	76			
4	94	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	71	69			
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			
6	83	72	65	61	81	71	65	60	70	64	60	68	63	59	67	63	59	57			
7	78	67	60	55	76	66	60	55	65	59	55	64	58	55	63	58	54	53			
8	73	62	56	51	72	62	55	51	61	55	51	59	54	50	58	54	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206884

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	239.3	6.8
10°-20°	678.1	19.2
20°-30°	972.5	27.6
30°-40°	915.7	26.0
40°-50°	505.7	14.3
50°-60°	162.2	4.6
60°-70°	40.6	1.2
70°-80°	9.6	0.3
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1889.9	53.6
0°-40°	2805.6	79.6
0°-60°	3473.5	98.6
0°-90°	3524.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3524.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2537	
5°	2525	239
15°	2402	678
25°	2133	973
35°	1485	916
45°	642	506
55°	165	162
65°	37	41
75°	6	10
85°	0	1
90°	0	



TEST NUMBER: P206884

CATALOG NUMBER: LD4B50D010TE EU4B30508040 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2536.8
2.5°	2518.5
5°	2524.6
7.5°	2506.3
10°	2475.7
12.5°	2445.1
15°	2402.3
17.5°	2365.7
20°	2304.5
22.5°	2219.0
25°	2133.4
27.5°	2017.2
30°	1864.4
32.5°	1693.2
35°	1485.4
37.5°	1265.4
40°	1039.2
42.5°	831.3
45°	641.8
47.5°	482.9
50°	348.4
52.5°	244.5
55°	165.0
57.5°	110.0
60°	79.5
62.5°	55.0
65°	36.7
67.5°	24.5
70°	18.3
72.5°	12.2
75°	6.1
77.5°	6.1
80°	6.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)