

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252124

Luminaire Tested: **LD4B50D010TE EU4B30509040 4LBBA1MB**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P252124  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-4)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30509040 4LBBA1MB  
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE BLACK TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2254.9 lumens  
Efficiency: N/A  
Efficacy: 38.4 lumens/watt  
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.94  
Luminous Opening: Circular (Dia: 0.38' x H: 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P252124

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBBA1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P252124

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBBA1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	219787
5°	219189
10°	217062
15°	213587
20°	207332
25°	191538
30°	155388
35°	96322
40°	45317
45°	15822
50°	4458
55°	3007
60°	2300
65°	2029
70°	1681
75°	1092
80°	1628
85°	0



TEST NUMBER: P252124

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBBA1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	212.3	9.4
10°-20°	595.0	26.4
20°-30°	799.8	35.5
30°-40°	510.9	22.7
40°-50°	108.6	4.8
50°-60°	16.4	0.7
60°-70°	8.0	0.4
70°-80°	3.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1607.1	71.3
0°-40°	2118.1	93.9
0°-60°	2243.1	99.5
0°-90°	2254.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2254.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2255	
5°	2240	212
15°	2117	595
25°	1781	800
35°	810	511
45°	115	109
55°	18	16
65°	9	8
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P252124

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBBA1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2255.2
2.5°	2252.3
5°	2240.5
7.5°	2219.9
10°	2193.4
12.5°	2158.1
15°	2116.9
17.5°	2063.9
20°	1999.1
22.5°	1907.8
25°	1781.2
27.5°	1604.6
30°	1380.8
32.5°	1104.1
35°	809.6
37.5°	553.5
40°	356.2
42.5°	212.0
45°	114.8
47.5°	58.9
50°	29.4
52.5°	20.6
55°	17.7
57.5°	14.7
60°	11.8
62.5°	8.8
65°	8.8
67.5°	5.9
70°	5.9
72.5°	2.9
75°	2.9
77.5°	2.9
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)