

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208225

Luminaire Tested: **LD4B50D010TE EU4B30509040 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509040 4LBML1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4231.8 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208225

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208225

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208225

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	604.0	14.3
10°-20°	1350.4	31.9
20°-30°	1342.6	31.7
30°-40°	731.1	17.3
40°-50°	169.0	4.0
50°-60°	23.8	0.6
60°-70°	8.8	0.2
70°-80°	2.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3297.0	77.9
0°-40°	4028.2	95.2
0°-60°	4221.0	99.7
0°-90°	4231.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4231.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6671	
5°	6533	604
15°	4874	1350
25°	2944	1343
35°	1132	731
45°	195	169
55°	26	24
65°	10	9
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P208225

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	6671.3
2.5°	6655.9
5°	6533.1
7.5°	6282.2
10°	5934.0
12.5°	5422.0
15°	4874.2
17.5°	4331.5
20°	3799.0
22.5°	3363.8
25°	2944.0
27.5°	2544.6
30°	2094.1
32.5°	1592.3
35°	1131.5
37.5°	762.9
40°	496.6
42.5°	312.3
45°	194.6
47.5°	112.6
50°	56.3
52.5°	30.7
55°	25.6
57.5°	15.4
60°	15.4
62.5°	10.2
65°	10.2
67.5°	5.1
70°	5.1
72.5°	5.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)