

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839424

Luminaire Tested: **LD4C90D010 EU4909035 4LBSLI**

Issue Date: 2/9/2022

Test Information

Test Method: LM-79-08
Report Number: P839424
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C90D010 EU4909035 4LBSLI
Description: 4 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9845.0 lumens
Efficiency: N/A
Efficacy: 101.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839424
CATALOG NUMBER: LD4C90D010 EU4909035 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839424

CATALOG NUMBER: LD4C90D010 EU4909035 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	863623
5°	844058
10°	792641
15°	737432
20°	683942
25°	623453
30°	555052
35°	491983
40°	442199
45°	395765
50°	339516
55°	273112
60°	203494
65°	129912
70°	62608
75°	10395
80°	7641
85°	0



TEST NUMBER: P839424

CATALOG NUMBER: LD4C90D010 EU4909035 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	637.4	6.5
10°-20°	1625.6	16.5
20°-30°	2106.5	21.4
30°-40°	2064.0	21.0
40°-50°	1749.5	17.8
50°-60°	1146.8	11.6
60°-70°	461.0	4.7
70°-80°	52.7	0.5
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4369.6	44.4
0°-40°	6433.6	65.3
0°-60°	9329.9	94.8
0°-90°	9845.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9845.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7030	
5°	6844	637
15°	5798	1626
25°	4599	2107
35°	3280	2064
45°	2278	1749
55°	1275	1147
65°	447	461
75°	22	53
85°	0	1
90°	0	



TEST NUMBER: P839424

CATALOG NUMBER: LD4C90D010 EU4909035 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7029.7
2.5°	6975.1
5°	6844.3
7.5°	6626.3
10°	6353.9
12.5°	6059.6
15°	5798.0
17.5°	5514.8
20°	5231.4
22.5°	4926.3
25°	4599.3
27.5°	4261.3
30°	3912.7
32.5°	3585.8
35°	3280.4
37.5°	3029.9
40°	2757.3
42.5°	2517.6
45°	2277.9
47.5°	2027.2
50°	1776.4
52.5°	1525.9
55°	1275.1
57.5°	1046.3
60°	828.2
62.5°	632.0
65°	446.9
67.5°	294.3
70°	174.3
72.5°	76.2
75°	21.9
77.5°	10.8
80°	10.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)