

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839429

Luminaire Tested: **LD4C90D010 EU4909050 4LBSH**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839429  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C90D010 EU4909050 4LBSH  
Description: 4 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9648.0 lumens  
Efficiency: N/A  
Efficacy: 99.4 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 97.1  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839429

CATALOG NUMBER: LD4C90D010 EU4909050 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P839429

CATALOG NUMBER: LD4C90D010 EU4909050 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	619894
5°	617033
10°	604295
15°	582327
20°	555519
25°	525583
30°	495783
35°	466802
40°	439520
45°	409716
50°	373594
55°	329936
60°	279271
65°	219243
70°	156503
75°	85725
80°	15140
85°	0



TEST NUMBER: P839429

CATALOG NUMBER: LD4C90D010 EU4909050 4LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	472.6	4.9
10°-20°	1284.6	13.3
20°-30°	1784.0	18.5
30°-40°	1946.8	20.2
40°-50°	1816.0	18.8
50°-60°	1378.4	14.3
60°-70°	754.8	7.8
70°-80°	207.7	2.2
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3541.3	36.7
0°-40°	5488.1	56.9
0°-60°	8682.6	90.0
0°-90°	9648.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9648.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5046	
5°	5003	473
15°	4578	1285
25°	3877	1784
35°	3112	1947
45°	2358	1816
55°	1540	1378
65°	754	755
75°	181	208
85°	0	3
90°	0	



TEST NUMBER: P839429

CATALOG NUMBER: LD4C90D010 EU4909050 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5045.8
2.5°	5045.8
5°	5003.4
7.5°	4939.8
10°	4844.1
12.5°	4716.7
15°	4578.5
17.5°	4408.7
20°	4249.1
22.5°	4057.9
25°	3877.3
27.5°	3696.9
30°	3494.9
32.5°	3303.7
35°	3112.5
37.5°	2921.3
40°	2740.6
42.5°	2549.4
45°	2358.2
47.5°	2167.0
50°	1954.7
52.5°	1752.7
55°	1540.4
57.5°	1338.4
60°	1136.6
62.5°	934.9
65°	754.2
67.5°	584.2
70°	435.7
72.5°	297.5
75°	180.6
77.5°	84.9
80°	21.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)