

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207096

Luminaire Tested: **LD4B50D010TE EU4B30509040 4LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207096  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30509040 4LBWMW1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3940.1 lumens  
Efficiency: N/A  
Efficacy: 67.0 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207096

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P207096

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61																			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55																			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50																			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45																			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38																			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207096

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	224.2	5.7
10°-20°	626.9	15.9
20°-30°	886.0	22.5
30°-40°	858.2	21.8
40°-50°	579.1	14.7
50°-60°	359.4	9.1
60°-70°	240.2	6.1
70°-80°	131.4	3.3
80°-90°	34.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1737.0	44.1
0°-40°	2595.2	65.9
0°-60°	3533.7	89.7
0°-90°	3940.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3940.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2388	
5°	2367	224
15°	2224	627
25°	1943	886
35°	1380	858
45°	741	579
55°	394	359
65°	240	240
75°	123	131
85°	31	35
90°	0	



TEST NUMBER: P207096

CATALOG NUMBER: LD4B50D010TE EU4B30509040 4LBWMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2387.6
2.5°	2387.6
5°	2367.2
7.5°	2341.6
10°	2310.9
12.5°	2280.3
15°	2224.0
17.5°	2178.0
20°	2101.3
22.5°	2024.6
25°	1942.8
27.5°	1830.3
30°	1707.6
32.5°	1549.1
35°	1380.4
37.5°	1211.7
40°	1043.0
42.5°	874.3
45°	741.3
47.5°	618.6
50°	526.6
52.5°	449.9
55°	393.7
57.5°	347.7
60°	311.9
62.5°	276.1
65°	240.3
67.5°	209.6
70°	178.9
72.5°	153.4
75°	122.7
77.5°	97.1
80°	71.6
82.5°	51.1
85°	30.7
87.5°	10.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)