

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208220

Luminaire Tested: **LD4B50D010TE EU4B30508050 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208220
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508050 4LBMLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5048.9 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208220

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208220

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | | | |
| 2 | 109 | 104 | 100 | 97 | 107 | 102 | 99 | 96 | 99 | 96 | 94 | 96 | 94 | 92 | 94 | 92 | 90 | 88 | | | |
| 3 | 104 | 98 | 93 | 89 | 102 | 96 | 92 | 89 | 94 | 90 | 87 | 91 | 88 | 86 | 89 | 87 | 85 | 83 | | | |
| 4 | 99 | 92 | 87 | 83 | 97 | 91 | 86 | 82 | 89 | 85 | 81 | 87 | 83 | 80 | 85 | 82 | 79 | 78 | | | |
| 5 | 94 | 87 | 81 | 77 | 93 | 86 | 81 | 77 | 84 | 79 | 76 | 82 | 78 | 75 | 81 | 77 | 75 | 73 | | | |
| 6 | 90 | 82 | 76 | 72 | 89 | 81 | 76 | 72 | 80 | 75 | 71 | 78 | 74 | 71 | 77 | 73 | 71 | 69 | | | |
| 7 | 86 | 77 | 72 | 68 | 85 | 77 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 73 | 69 | 67 | 65 | | | |
| 8 | 82 | 73 | 68 | 64 | 81 | 73 | 67 | 64 | 72 | 67 | 64 | 71 | 66 | 63 | 70 | 66 | 63 | 62 | | | |
| 9 | 79 | 70 | 64 | 60 | 78 | 69 | 64 | 60 | 68 | 63 | 60 | 67 | 63 | 60 | 67 | 63 | 60 | 58 | | | |
| 10 | 75 | 66 | 61 | 57 | 74 | 66 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 57 | 64 | 60 | 57 | 56 | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208220

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBMLI1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 720.7 | 14.3 |
| 10°-20° | 1611.1 | 31.9 |
| 20°-30° | 1601.8 | 31.7 |
| 30°-40° | 872.3 | 17.3 |
| 40°-50° | 201.6 | 4.0 |
| 50°-60° | 28.4 | 0.6 |
| 60°-70° | 10.5 | 0.2 |
| 70°-80° | 2.4 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 3933.6 | 77.9 |
| 0°-40° | 4806.0 | 95.2 |
| 0°-60° | 5035.9 | 99.7 |
| 0°-90° | 5048.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5048.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 7959 | |
| 5° | 7794 | 721 |
| 15° | 5815 | 1611 |
| 25° | 3512 | 1602 |
| 35° | 1350 | 872 |
| 45° | 232 | 202 |
| 55° | 30 | 28 |
| 65° | 12 | 11 |
| 75° | 0 | 2 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P208220

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBML1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 7959.4 |
| 2.5° | 7941.1 |
| 5° | 7794.5 |
| 7.5° | 7495.2 |
| 10° | 7079.8 |
| 12.5° | 6468.9 |
| 15° | 5815.3 |
| 17.5° | 5167.8 |
| 20° | 4532.5 |
| 22.5° | 4013.3 |
| 25° | 3512.4 |
| 27.5° | 3035.9 |
| 30° | 2498.4 |
| 32.5° | 1899.8 |
| 35° | 1350.0 |
| 37.5° | 910.2 |
| 40° | 592.5 |
| 42.5° | 372.6 |
| 45° | 232.1 |
| 47.5° | 134.4 |
| 50° | 67.2 |
| 52.5° | 36.7 |
| 55° | 30.5 |
| 57.5° | 18.3 |
| 60° | 18.3 |
| 62.5° | 12.2 |
| 65° | 12.2 |
| 67.5° | 6.1 |
| 70° | 6.1 |
| 72.5° | 6.1 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)