

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839436

Luminaire Tested: **LD6C05D010 EU6059027 6LCSQWLI**

Issue Date: 6/29/2023



Test Information

Test Method: LM-79-08
Report Number: P839436
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C05D010 EU6059027 6LCSQWLI
Description: 6 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND 6LCSQW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 635.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839436

CATALOG NUMBER: LD6C05D010 EU6059027 6LCSQWLI

Luminous Intensity Polar Plot





TEST NUMBER: P839436

CATALOG NUMBER: LD6C05D010 EU6059027 6LCSQWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12822
5°	12802
10°	12731
15°	12583
20°	12357
25°	12090
30°	11803
35°	11464
40°	11005
45°	10205
50°	8795
55°	7011
60°	5459
65°	4085
70°	2971
75°	2346
80°	2207
85°	2174



TEST NUMBER: P839436

CATALOG NUMBER: LD6C05D010 EU6059027 6LCSQWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.1	4.4
10°-20°	79.5	12.5
20°-30°	117.2	18.5
30°-40°	136.1	21.4
40°-50°	127.9	20.1
50°-60°	84.7	13.3
60°-70°	40.8	6.4
70°-80°	15.7	2.5
80°-90°	4.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	224.8	35.4
0°-40°	360.9	56.8
0°-60°	573.6	90.3
0°-90°	635.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	635.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	298	
5°	296	28
15°	282	80
25°	254	117
35°	218	136
45°	168	128
55°	93	85
65°	40	41
75°	14	16
85°	4	5
90°	0	



TEST NUMBER: P839436

CATALOG NUMBER: LD6C05D010 EU6059027 6LCSQWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	297.8
2.5°	297.5
5°	296.2
7.5°	294.2
10°	291.2
12.5°	287.2
15°	282.3
17.5°	276.4
20°	269.7
22.5°	262.3
25°	254.5
27.5°	246.1
30°	237.4
32.5°	228.1
35°	218.1
37.5°	207.2
40°	195.8
42.5°	182.8
45°	167.6
47.5°	150.4
50°	131.3
52.5°	111.9
55°	93.4
57.5°	77.5
60°	63.4
62.5°	50.8
65°	40.1
67.5°	31.1
70°	23.6
72.5°	17.9
75°	14.1
77.5°	11.4
80°	8.9
82.5°	6.6
85°	4.4
87.5°	2.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)