

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207606

Luminaire Tested: **LD4B50D010TE EU4B30508050 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508050 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4212.5 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207606

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207606

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89			
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80			
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64			
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53			
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42			
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207606

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	296.4	7.0
10°-20°	794.6	18.9
20°-30°	1056.6	25.1
30°-40°	864.1	20.5
40°-50°	503.3	11.9
50°-60°	333.8	7.9
60°-70°	219.5	5.2
70°-80°	115.8	2.7
80°-90°	28.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2147.6	51.0
0°-40°	3011.8	71.5
0°-60°	3848.9	91.4
0°-90°	4212.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4212.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3198	
5°	3161	296
15°	2832	795
25°	2319	1057
35°	1379	864
45°	635	503
55°	372	334
65°	220	220
75°	110	116
85°	24	28
90°	0	



TEST NUMBER: P207606

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3197.8
2.5°	3191.7
5°	3161.2
7.5°	3088.0
10°	3008.6
12.5°	2935.4
15°	2831.7
17.5°	2715.7
20°	2618.1
22.5°	2483.8
25°	2319.0
27.5°	2142.1
30°	1916.3
32.5°	1647.7
35°	1379.2
37.5°	1135.1
40°	921.5
42.5°	756.7
45°	634.7
47.5°	537.0
50°	469.9
52.5°	415.0
55°	372.3
57.5°	329.5
60°	286.8
62.5°	256.3
65°	219.7
67.5°	189.2
70°	158.7
72.5°	134.3
75°	109.8
77.5°	85.4
80°	61.0
82.5°	42.7
85°	24.4
87.5°	6.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)