

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839437

Luminaire Tested: **LD6C05D010 EU6059030 6LCSQWLI**

Issue Date: 6/29/2023



Test Information

Test Method: LM-79-08
Report Number: P839437
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C05D010 EU6059030 6LCSQWLI
Description: 6 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LCSQW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 660.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839437

CATALOG NUMBER: LD6C05D010 EU6059030 6LCSQWLI

Luminous Intensity Polar Plot





TEST NUMBER: P839437

CATALOG NUMBER: LD6C05D010 EU6059030 6LCSQWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13326
5°	13307
10°	13234
15°	13078
20°	12843
25°	12566
30°	12265
35°	11916
40°	11438
45°	10607
50°	9136
55°	7289
60°	5675
65°	4248
70°	3084
75°	2445
80°	2281
85°	2272



TEST NUMBER: P839437

CATALOG NUMBER: LD6C05D010 EU6059030 6LCSQWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.2	4.4
10°-20°	82.6	12.5
20°-30°	121.8	18.5
30°-40°	141.5	21.4
40°-50°	133.0	20.1
50°-60°	88.0	13.3
60°-70°	42.4	6.4
70°-80°	16.4	2.5
80°-90°	5.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.7	35.4
0°-40°	375.1	56.8
0°-60°	596.1	90.3
0°-90°	660.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	660.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	310	
5°	308	29
15°	293	83
25°	264	122
35°	227	141
45°	174	133
55°	97	88
65°	42	42
75°	15	16
85°	5	5
90°	0	



TEST NUMBER: P839437

CATALOG NUMBER: LD6C05D010 EU6059030 6LCSQWLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	309.5
2.5°	309.3
5°	307.9
7.5°	305.8
10°	302.7
12.5°	298.5
15°	293.4
17.5°	287.3
20°	280.3
22.5°	272.6
25°	264.5
27.5°	255.8
30°	246.7
32.5°	237.0
35°	226.7
37.5°	215.4
40°	203.5
42.5°	190.0
45°	174.2
47.5°	156.3
50°	136.4
52.5°	116.3
55°	97.1
57.5°	80.6
60°	65.9
62.5°	52.8
65°	41.7
67.5°	32.3
70°	24.5
72.5°	18.6
75°	14.7
77.5°	11.9
80°	9.2
82.5°	6.9
85°	4.6
87.5°	2.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)