

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206162

Luminaire Tested: **LD4B50D010TE EU4B30508050 4LBSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206162  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B50D010TE EU4B30508050 4LB5MW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM  
SINGLE DRIVER D010TE  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5512.9 lumens  
Efficiency: N/A  
Efficacy: 93.8 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 58.77  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206162

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P206162

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206162

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	210.5	3.8
10°-20°	599.9	10.9
20°-30°	903.5	16.4
30°-40°	1075.1	19.5
40°-50°	1073.1	19.5
50°-60°	872.7	15.8
60°-70°	536.9	9.7
70°-80°	208.0	3.8
80°-90°	33.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1713.8	31.1
0°-40°	2788.9	50.6
0°-60°	4734.7	85.9
0°-90°	5512.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5512.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2221	
5°	2215	210
15°	2130	600
25°	1966	903
35°	1721	1075
45°	1395	1073
55°	977	873
65°	539	537
75°	190	208
85°	26	33
90°	0	



TEST NUMBER: P206162

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2221.2
2.5°	2224.4
5°	2214.6
7.5°	2201.6
10°	2185.2
12.5°	2155.8
15°	2129.7
17.5°	2090.5
20°	2048.0
22.5°	2008.8
25°	1966.4
27.5°	1907.6
30°	1848.8
32.5°	1793.3
35°	1721.4
37.5°	1643.0
40°	1571.1
42.5°	1482.9
45°	1394.8
47.5°	1300.0
50°	1198.8
52.5°	1094.2
55°	976.7
57.5°	862.3
60°	751.3
62.5°	643.5
65°	539.0
67.5°	441.0
70°	349.5
72.5°	264.6
75°	189.5
77.5°	124.1
80°	75.1
82.5°	45.7
85°	26.1
87.5°	13.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)