

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839439

Luminaire Tested: **LD6C05D010 EU6059040 6LCSQWLI**

Issue Date: 6/29/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P839439  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/29/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C05D010 EU6059040 6LCSQWLI  
Description: 6 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND 6LCSQW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 670.0 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839439

CATALOG NUMBER: LD6C05D010 EU6059040 6LCSQWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P839439

CATALOG NUMBER: LD6C05D010 EU6059040 6LCSQWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	13528
5°	13506
10°	13435
15°	13279
20°	13035
25°	12756
30°	12449
35°	12094
40°	11606
45°	10771
50°	9277
55°	7401
60°	5761
65°	4309
70°	3135
75°	2479
80°	2331
85°	2322



TEST NUMBER: P839439

CATALOG NUMBER: LD6C05D010 EU6059040 6LCSQWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	29.7	4.4
10°-20°	83.9	12.5
20°-30°	123.6	18.5
30°-40°	143.6	21.4
40°-50°	135.0	20.1
50°-60°	89.3	13.3
60°-70°	43.1	6.4
70°-80°	16.6	2.5
80°-90°	5.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	237.2	35.4
0°-40°	380.8	56.8
0°-60°	605.1	90.3
0°-90°	670.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	670.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	314	
5°	312	30
15°	298	84
25°	268	124
35°	230	144
45°	177	135
55°	99	89
65°	42	43
75°	15	17
85°	5	5
90°	0	



TEST NUMBER: P839439

CATALOG NUMBER: LD6C05D010 EU6059040 6LCSQWLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	314.2
2.5°	313.9
5°	312.5
7.5°	310.4
10°	307.3
12.5°	303.0
15°	297.9
17.5°	291.6
20°	284.5
22.5°	276.7
25°	268.5
27.5°	259.7
30°	250.4
32.5°	240.6
35°	230.1
37.5°	218.6
40°	206.5
42.5°	192.9
45°	176.9
47.5°	158.7
50°	138.5
52.5°	118.0
55°	98.6
57.5°	81.8
60°	66.9
62.5°	53.6
65°	42.3
67.5°	32.8
70°	24.9
72.5°	18.9
75°	14.9
77.5°	12.1
80°	9.4
82.5°	7.0
85°	4.7
87.5°	2.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)