

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207091

Luminaire Tested: **LD4B50D010TE EU4B30508050 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207091
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508050 4LBWMW1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4700.9 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207091

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207091

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78																			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69																			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61																			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55																			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50																			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45																			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38																			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207091

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.5	5.7
10°-20°	747.9	15.9
20°-30°	1057.0	22.5
30°-40°	1023.9	21.8
40°-50°	690.9	14.7
50°-60°	428.8	9.1
60°-70°	286.6	6.1
70°-80°	156.8	3.3
80°-90°	41.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2072.4	44.1
0°-40°	3096.3	65.9
0°-60°	4216.0	89.7
0°-90°	4700.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4700.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2849	
5°	2824	267
15°	2653	748
25°	2318	1057
35°	1647	1024
45°	884	691
55°	470	429
65°	287	287
75°	146	157
85°	37	41
90°	0	



TEST NUMBER: P207091

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2848.6
2.5°	2848.6
5°	2824.2
7.5°	2793.7
10°	2757.1
12.5°	2720.5
15°	2653.4
17.5°	2598.5
20°	2507.0
22.5°	2415.5
25°	2317.9
27.5°	2183.7
30°	2037.3
32.5°	1848.3
35°	1647.0
37.5°	1445.7
40°	1244.4
42.5°	1043.1
45°	884.5
47.5°	738.1
50°	628.3
52.5°	536.8
55°	469.7
57.5°	414.8
60°	372.1
62.5°	329.4
65°	286.7
67.5°	250.1
70°	213.5
72.5°	183.0
75°	146.4
77.5°	115.9
80°	85.4
82.5°	61.0
85°	36.6
87.5°	12.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)