

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206782

Luminaire Tested: **LD4B50D010TE EU4B30508050 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206782
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30508050 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4670.4 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206782

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206782

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92																
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	85	84			84																
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			76																
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69																
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63			63																
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58			58																
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53			53																
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49			49																
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45			45																
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			41																

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206782

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.9	6.1
10°-20°	875.3	18.7
20°-30°	1346.4	28.8
30°-40°	1299.1	27.8
40°-50°	677.3	14.5
50°-60°	142.6	3.1
60°-70°	33.1	0.7
70°-80°	12.8	0.3
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2504.6	53.6
0°-40°	3803.7	81.4
0°-60°	4623.6	99.0
0°-90°	4670.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4670.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2920	
5°	2945	283
15°	3097	875
25°	2951	1346
35°	2108	1299
45°	861	677
55°	128	143
65°	30	33
75°	12	13
85°	0	1
90°	0	



TEST NUMBER: P206782

CATALOG NUMBER: LD4B50D010TE EU4B30508050 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2920.1
2.5°	2926.2
5°	2944.6
7.5°	2969.0
10°	3005.7
12.5°	3054.5
15°	3097.3
17.5°	3121.7
20°	3103.4
22.5°	3066.8
25°	2950.7
27.5°	2810.2
30°	2626.9
32.5°	2382.5
35°	2107.6
37.5°	1808.3
40°	1496.7
42.5°	1185.2
45°	861.4
47.5°	580.4
50°	372.7
52.5°	226.0
55°	128.3
57.5°	79.4
60°	55.0
62.5°	42.8
65°	30.5
67.5°	24.4
70°	18.3
72.5°	18.3
75°	12.2
77.5°	6.1
80°	6.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)