

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839491

Luminaire Tested: **LD6C35D010 EU6359027 6LCSQWLI**

Issue Date: 6/29/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P839491  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/29/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C35D010 EU6359027 6LCSQWLI  
Description: 6 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LCSQW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3365.0 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839491

CATALOG NUMBER: LD6C35D010 EU6359027 6LCSQWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P839491

CATALOG NUMBER: LD6C35D010 EU6359027 6LCSQWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	67946
5°	67838
10°	67468
15°	66688
20°	65475
25°	64058
30°	62533
35°	60750
40°	58307
45°	54082
50°	46593
55°	37165
60°	28933
65°	21659
70°	15723
75°	12460
80°	11678
85°	11609



TEST NUMBER: P839491

CATALOG NUMBER: LD6C35D010 EU6359027 6LCSQWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.0	4.4
10°-20°	421.3	12.5
20°-30°	620.9	18.5
30°-40°	721.3	21.4
40°-50°	678.0	20.1
50°-60°	448.8	13.3
60°-70°	216.3	6.4
70°-80°	83.4	2.5
80°-90°	26.0	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1191.2	35.4
0°-40°	1912.5	56.8
0°-60°	3039.3	90.3
0°-90°	3365.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3365.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1578	
5°	1570	149
15°	1496	421
25°	1348	621
35°	1156	721
45°	888	678
55°	495	449
65°	213	216
75°	75	83
85°	24	26
90°	0	



TEST NUMBER: P839491

CATALOG NUMBER: LD6C35D010 EU6359027 6LCSQWLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1578.1
2.5°	1576.7
5°	1569.6
7.5°	1558.9
10°	1543.2
12.5°	1521.8
15°	1496.1
17.5°	1464.7
20°	1429.0
22.5°	1389.8
25°	1348.4
27.5°	1304.2
30°	1257.8
32.5°	1208.6
35°	1155.8
37.5°	1098.0
40°	1037.4
42.5°	968.9
45°	888.2
47.5°	796.9
50°	695.6
52.5°	592.9
55°	495.1
57.5°	410.9
60°	336.0
62.5°	269.0
65°	212.6
67.5°	164.8
70°	124.9
72.5°	94.9
75°	74.9
77.5°	60.6
80°	47.1
82.5°	35.0
85°	23.5
87.5°	13.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)