

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208125

Luminaire Tested: **LD4B50D010TE EU4B30509050 4LBWL11**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208125
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B50D010TE EU4B30509050 4LBWLI1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
SINGLE DRIVER D010TE
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4486.7 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 58.77
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208125

CATALOG NUMBER: LD4B50D010TE EU4B30509050 4LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P208125

CATALOG NUMBER: LD4B50D010TE EU4B30509050 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208125

CATALOG NUMBER: LD4B50D010TE EU4B30509050 4LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	268.8	6.0
10°-20°	848.4	18.9
20°-30°	1323.5	29.5
30°-40°	1287.8	28.7
40°-50°	643.2	14.3
50°-60°	99.6	2.2
60°-70°	12.0	0.3
70°-80°	3.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2440.8	54.4
0°-40°	3728.5	83.1
0°-60°	4471.3	99.7
0°-90°	4486.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4486.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2749	
5°	2785	269
15°	2996	848
25°	2908	1324
35°	2091	1288
45°	807	643
55°	82	100
65°	10	12
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P208125

CATALOG NUMBER: LD4B50D010TE EU4B30509050 4LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2749.1
2.5°	2759.4
5°	2785.1
7.5°	2826.2
10°	2877.5
12.5°	2944.3
15°	2995.7
17.5°	3036.8
20°	3042.0
22.5°	3006.0
25°	2908.4
27.5°	2764.5
30°	2584.7
32.5°	2358.6
35°	2091.4
37.5°	1798.5
40°	1490.2
42.5°	1161.3
45°	806.7
47.5°	519.0
50°	313.4
52.5°	169.6
55°	82.2
57.5°	36.0
60°	20.6
62.5°	15.4
65°	10.3
67.5°	10.3
70°	5.1
72.5°	5.1
75°	5.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)