

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274271

Luminaire Tested: **LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274271
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35173)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0H
Description: PORTFOLIO 4" W2N RN DOWNLIGHT, MEDIUM DISTRIBUTION WITH HAZE FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 810.6 lumens
Efficiency: N/A
Efficacy: 57.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274271

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0H

Luminous Intensity Polar Plot





TEST NUMBER: P274271

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87824
5°	86558
10°	82943
15°	78332
20°	73124
25°	66378
30°	55411
35°	40148
40°	25131
45°	14370
50°	7479
55°	4191
60°	2666
65°	1577
70°	1182
75°	507
80°	755
85°	0



TEST NUMBER: P274271

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.0	9.1
10°-20°	194.0	23.9
20°-30°	249.4	30.8
30°-40°	187.6	23.1
40°-50°	75.3	9.3
50°-60°	21.4	2.6
60°-70°	6.8	0.8
70°-80°	1.9	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.4	63.8
0°-40°	705.0	87.0
0°-60°	801.8	98.9
0°-90°	810.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	810.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	804	
5°	789	74
15°	692	194
25°	551	249
35°	301	188
45°	93	75
55°	22	21
65°	6	7
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P274271

CATALOG NUMBER: LD4B10DE010W2N2765 EU4B1020W2N902765 4LBM0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	803.8
2.5°	799.0
5°	789.2
7.5°	770.8
10°	747.6
12.5°	719.4
15°	692.5
17.5°	661.9
20°	628.9
22.5°	593.4
25°	550.6
27.5°	499.2
30°	439.2
32.5°	371.9
35°	301.0
37.5°	234.9
40°	176.2
42.5°	129.7
45°	93.0
47.5°	63.6
50°	44.0
52.5°	30.6
55°	22.0
57.5°	15.9
60°	12.2
62.5°	8.6
65°	6.1
67.5°	4.9
70°	3.7
72.5°	2.4
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)