

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839502

Luminaire Tested: **LD6C45D010 EU6459030 6LCSQWLI**

Issue Date: 6/29/2023

Test Information

Test Method: LM-79-08
Report Number: P839502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)
Test Lab: INNOVATION CENTER
Issue Date: 6/29/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C45D010 EU6459030 6LCSQWLI
Description: 6 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LCSQW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4700.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839502

CATALOG NUMBER: LD6C45D010 EU6459030 6LCSQWLI

Luminous Intensity Polar Plot





TEST NUMBER: P839502

CATALOG NUMBER: LD6C45D010 EU6459030 6LCSQWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94903
5°	94751
10°	94234
15°	93147
20°	91454
25°	89474
30°	87342
35°	84850
40°	81436
45°	75540
50°	65080
55°	51915
60°	40412
65°	30258
70°	21955
75°	17401
80°	16315
85°	16253



TEST NUMBER: P839502

CATALOG NUMBER: LD6C45D010 EU6459030 6LCSQWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	208.1	4.4
10°-20°	588.5	12.5
20°-30°	867.2	18.5
30°-40°	1007.4	21.4
40°-50°	947.0	20.1
50°-60°	626.9	13.3
60°-70°	302.1	6.4
70°-80°	116.5	2.5
80°-90°	36.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1663.9	35.4
0°-40°	2671.3	56.8
0°-60°	4245.1	90.3
0°-90°	4700.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4700.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2204	
5°	2192	208
15°	2090	588
25°	1883	867
35°	1614	1007
45°	1241	947
55°	692	627
65°	297	302
75°	105	116
85°	33	36
90°	0	



TEST NUMBER: P839502

CATALOG NUMBER: LD6C45D010 EU6459030 6LCSQWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2204.2
2.5°	2202.3
5°	2192.3
7.5°	2177.3
10°	2155.4
12.5°	2125.5
15°	2089.7
17.5°	2045.8
20°	1996.0
22.5°	1941.2
25°	1883.4
27.5°	1821.6
30°	1756.8
32.5°	1688.1
35°	1614.3
37.5°	1533.6
40°	1448.9
42.5°	1353.2
45°	1240.6
47.5°	1113.1
50°	971.6
52.5°	828.1
55°	691.6
57.5°	574.0
60°	469.3
62.5°	375.7
65°	297.0
67.5°	230.2
70°	174.4
72.5°	132.5
75°	104.6
77.5°	84.7
80°	65.8
82.5°	48.8
85°	32.9
87.5°	18.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)