

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839530

Luminaire Tested: **LD6C70D010 EU6709050 6LCSQWLI**

Issue Date: 6/29/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P839530  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/29/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C70D010 EU6709050 6LCSQWLI  
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LCSQW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7326.0 lumens  
Efficiency: N/A  
Efficacy: 93.9 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 78  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839530

CATALOG NUMBER: LD6C70D010 EU6709050 6LCSQWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P839530

CATALOG NUMBER: LD6C70D010 EU6709050 6LCSQWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	147931
5°	147692
10°	146886
15°	145188
20°	142552
25°	139465
30°	136143
35°	132260
40°	126934
45°	117749
50°	101439
55°	80920
60°	62999
65°	47159
70°	34216
75°	27132
80°	25415
85°	25343



TEST NUMBER: P839530

CATALOG NUMBER: LD6C70D010 EU6709050 6LCSQWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	324.4	4.4
10°-20°	917.3	12.5
20°-30°	1351.8	18.5
30°-40°	1570.3	21.4
40°-50°	1476.1	20.1
50°-60°	977.1	13.3
60°-70°	470.8	6.4
70°-80°	181.6	2.5
80°-90°	56.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2593.5	35.4
0°-40°	4163.8	56.8
0°-60°	6617.0	90.3
0°-90°	7326.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7326.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3436	
5°	3417	324
15°	3257	917
25°	2936	1352
35°	2516	1570
45°	1934	1476
55°	1078	977
65°	463	471
75°	163	182
85°	51	57
90°	0	



TEST NUMBER: P839530

CATALOG NUMBER: LD6C70D010 EU6709050 6LCSQWLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3435.8
2.5°	3432.7
5°	3417.2
7.5°	3393.9
10°	3359.7
12.5°	3313.1
15°	3257.2
17.5°	3188.8
20°	3111.2
22.5°	3025.8
25°	2935.7
27.5°	2839.4
30°	2738.4
32.5°	2631.2
35°	2516.3
37.5°	2390.5
40°	2258.4
42.5°	2109.3
45°	1933.8
47.5°	1735.0
50°	1514.4
52.5°	1290.8
55°	1078.0
57.5°	894.7
60°	731.6
62.5°	585.6
65°	462.9
67.5°	358.8
70°	271.8
72.5°	206.6
75°	163.1
77.5°	132.0
80°	102.5
82.5°	76.1
85°	51.3
87.5°	29.5
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)