

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839555

Luminaire Tested: **LDS4C05D010 EU4059027 4LBSWMH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839555
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C05D010 EU4059027 4LBSWMH
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND 4LBS TRIM WITH WMH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 549.0 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839555

CATALOG NUMBER: LDS4C05D010 EU4059027 4LBSWMH

Luminous Intensity Polar Plot





TEST NUMBER: P839555

CATALOG NUMBER: LDS4C05D010 EU4059027 4LBSWMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35271
5°	35110
10°	34381
15°	33132
20°	31612
25°	29903
30°	28216
35°	26561
40°	25002
45°	23316
50°	21253
55°	18784
60°	15897
65°	12471
70°	8908
75°	4889
80°	849
85°	0



TEST NUMBER: P839555

CATALOG NUMBER: LDS4C05D010 EU4059027 4LBSWMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.9	4.9
10°-20°	73.1	13.3
20°-30°	101.5	18.5
30°-40°	110.8	20.2
40°-50°	103.3	18.8
50°-60°	78.4	14.3
60°-70°	42.9	7.8
70°-80°	11.8	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	201.5	36.7
0°-40°	312.3	56.9
0°-60°	494.1	90.0
0°-90°	549.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	549.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	287	
5°	285	27
15°	260	73
25°	221	102
35°	177	111
45°	134	103
55°	88	78
65°	43	43
75°	10	12
85°	0	0
90°	0	



TEST NUMBER: P839555

CATALOG NUMBER: LDS4C05D010 EU4059027 4LBSWMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	287.1
2.5°	287.1
5°	284.7
7.5°	281.1
10°	275.6
12.5°	268.4
15°	260.5
17.5°	250.9
20°	241.8
22.5°	230.9
25°	220.6
27.5°	210.4
30°	198.9
32.5°	188.0
35°	177.1
37.5°	166.2
40°	155.9
42.5°	145.1
45°	134.2
47.5°	123.3
50°	111.2
52.5°	99.7
55°	87.7
57.5°	76.2
60°	64.7
62.5°	53.2
65°	42.9
67.5°	33.2
70°	24.8
72.5°	16.9
75°	10.3
77.5°	4.8
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)