

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839558

Luminaire Tested: **LDS4C05D010 EU4059030 4LBPSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C05D010 EU4059030 4LBPSMB
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBPS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 513.0 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839558

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBPSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839558

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBPSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79	79	79	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70	70	70	70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62	62	62	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55	55	55	55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40	40	40	40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36	36	36	36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33	33	33	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33097
5°	32977
10°	32622
15°	32051
20°	31338
25°	30500
30°	29535
35°	28406
40°	26975
45°	24515
50°	20240
55°	14908
60°	10123
65°	5930
70°	2335
75°	522
80°	707
85°	1128



TEST NUMBER: P839558

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBPSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.3	4.9
10°-20°	71.0	13.8
20°-30°	103.5	20.2
30°-40°	118.2	23.0
40°-50°	107.4	20.9
50°-60°	63.4	12.4
60°-70°	21.3	4.1
70°-80°	2.2	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	199.8	39.0
0°-40°	318.0	62.0
0°-60°	488.7	95.3
0°-90°	513.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	513.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	269	
5°	267	25
15°	252	71
25°	225	104
35°	189	118
45°	141	107
55°	70	63
65°	20	21
75°	1	2
85°	1	1
90°	0	



TEST NUMBER: P839558

CATALOG NUMBER: LDS4C05D010 EU4059030 4LBPSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	269.4
2.5°	269.0
5°	267.4
7.5°	264.9
10°	261.5
12.5°	257.0
15°	252.0
17.5°	246.2
20°	239.7
22.5°	232.6
25°	225.0
27.5°	216.7
30°	208.2
32.5°	198.9
35°	189.4
37.5°	179.0
40°	168.2
42.5°	155.5
45°	141.1
47.5°	124.5
50°	105.9
52.5°	87.3
55°	69.6
57.5°	54.5
60°	41.2
62.5°	29.8
65°	20.4
67.5°	12.5
70°	6.5
72.5°	2.5
75°	1.1
77.5°	1.1
80°	1.0
82.5°	0.8
85°	0.8
87.5°	0.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)