

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839579

Luminaire Tested: **LDS4C05D010 EU4059040 4LBPSMMS**

Issue Date: 8/24/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P839579  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/24/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDS4C05D010 EU4059040 4LBPSMMS  
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND 4LBPS TRIM WITH MMS FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 533.0 lumens  
Efficiency: N/A  
Efficacy: 74.0 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839579

CATALOG NUMBER: LDS4C05D010 EU4059040 4LBPSMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P839579

CATALOG NUMBER: LDS4C05D010 EU4059040 4LBPSMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	34387
5°	34271
10°	33894
15°	33310
20°	32554
25°	31692
30°	30684
35°	29515
40°	28017
45°	25470
50°	21024
55°	15486
60°	10516
65°	6163
70°	2443
75°	570
80°	707
85°	1269



TEST NUMBER: P839579

CATALOG NUMBER: LDS4C05D010 EU4059040 4LBPSMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.3	4.9
10°-20°	73.7	13.8
20°-30°	107.5	20.2
30°-40°	122.8	23.0
40°-50°	111.6	20.9
50°-60°	65.8	12.3
60°-70°	22.1	4.1
70°-80°	2.3	0.4
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	207.6	38.9
0°-40°	330.4	62.0
0°-60°	507.8	95.3
0°-90°	533.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	533.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	280	
5°	278	26
15°	262	74
25°	234	108
35°	197	123
45°	147	112
55°	72	66
65°	21	22
75°	1	2
85°	1	1
90°	0	



TEST NUMBER: P839579

CATALOG NUMBER: LDS4C05D010 EU4059040 4LBPSMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	279.9
2.5°	279.4
5°	277.9
7.5°	275.3
10°	271.7
12.5°	267.0
15°	261.9
17.5°	255.8
20°	249.0
22.5°	241.7
25°	233.8
27.5°	225.1
30°	216.3
32.5°	206.7
35°	196.8
37.5°	186.0
40°	174.7
42.5°	161.6
45°	146.6
47.5°	129.3
50°	110.0
52.5°	90.7
55°	72.3
57.5°	56.6
60°	42.8
62.5°	31.0
65°	21.2
67.5°	13.0
70°	6.8
72.5°	2.6
75°	1.2
77.5°	1.2
80°	1.0
82.5°	0.9
85°	0.9
87.5°	0.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)