

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839158

Luminaire Tested: **LD4C05D010 EU4059050 4LBPSMW**

Issue Date: 6/29/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P839158  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/29/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C05D010 EU4059050 4LBPSMW  
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LBPS TRIM WITH MW FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 665.1 lumens  
Efficiency: N/A  
Efficacy: 92.4 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839158

CATALOG NUMBER: LD4C05D010 EU4059050 4LBPSMW

### Luminous Intensity Polar Plot





TEST NUMBER: P839158

CATALOG NUMBER: LD4C05D010 EU4059050 4LBPSMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88	88	88	88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66	66	66	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58	58	58	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51	51	51	51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46	46	46	46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41	41	41	41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37	37	37	37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33	33	33	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30	30	30	30

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	38318
5°	38255
10°	38048
15°	37609
20°	36920
25°	36125
30°	35266
35°	34255
40°	32877
45°	30492
50°	26280
55°	20948
60°	16315
65°	12209
70°	8872
75°	7025
80°	6580
85°	6625



TEST NUMBER: P839158

CATALOG NUMBER: LD4C05D010 EU4059050 4LBPSMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	29.4	4.4
10°-20°	83.3	12.5
20°-30°	122.7	18.5
30°-40°	142.5	21.4
40°-50°	134.0	20.1
50°-60°	88.7	13.3
60°-70°	42.8	6.4
70°-80°	16.5	2.5
80°-90°	5.2	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	235.4	35.4
0°-40°	378.0	56.8
0°-60°	600.6	90.3
0°-90°	665.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	665.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	312	
5°	310	29
15°	296	83
25°	266	123
35°	228	143
45°	176	134
55°	98	89
65°	42	43
75°	15	16
85°	5	5
90°	0	



TEST NUMBER: P839158

CATALOG NUMBER: LD4C05D010 EU4059050 4LBPSMW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	311.9
2.5°	311.6
5°	310.2
7.5°	308.1
10°	305.0
12.5°	300.7
15°	295.7
17.5°	289.5
20°	282.4
22.5°	274.7
25°	266.5
27.5°	257.7
30°	248.6
32.5°	238.8
35°	228.4
37.5°	217.0
40°	205.0
42.5°	191.5
45°	175.5
47.5°	157.5
50°	137.5
52.5°	117.2
55°	97.8
57.5°	81.2
60°	66.4
62.5°	53.2
65°	42.0
67.5°	32.6
70°	24.7
72.5°	18.8
75°	14.8
77.5°	12.0
80°	9.3
82.5°	6.9
85°	4.7
87.5°	2.7
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)