

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839160

Luminaire Tested: **LD4C05D010 EU4059050 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P839160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C05D010 EU4059050 4LBSLI
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 694.1 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839160

CATALOG NUMBER: LD4C05D010 EU4059050 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839160

CATALOG NUMBER: LD4C05D010 EU4059050 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90		
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80		
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71		
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63		
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57		
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51		
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60874
5°	59503
10°	55875
15°	51981
20°	48216
25°	43947
30°	39125
35°	34675
40°	31177
45°	27903
50°	23929
55°	19256
60°	14349
65°	9157
70°	4418
75°	712
80°	566
85°	0



TEST NUMBER: P839160

CATALOG NUMBER: LD4C05D010 EU4059050 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.9	6.5
10°-20°	114.6	16.5
20°-30°	148.5	21.4
30°-40°	145.5	21.0
40°-50°	123.3	17.8
50°-60°	80.9	11.7
60°-70°	32.5	4.7
70°-80°	3.7	0.5
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	308.0	44.4
0°-40°	453.5	65.3
0°-60°	657.7	94.8
0°-90°	694.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	694.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	496	
5°	482	45
15°	409	115
25°	324	148
35°	231	145
45°	161	123
55°	90	81
65°	32	32
75°	2	4
85°	0	0
90°	0	



TEST NUMBER: P839160

CATALOG NUMBER: LD4C05D010 EU4059050 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	495.5
2.5°	491.7
5°	482.5
7.5°	467.1
10°	447.9
12.5°	427.2
15°	408.7
17.5°	388.8
20°	368.8
22.5°	347.3
25°	324.2
27.5°	300.4
30°	275.8
32.5°	252.8
35°	231.2
37.5°	213.6
40°	194.4
42.5°	177.5
45°	160.6
47.5°	142.9
50°	125.2
52.5°	107.6
55°	89.9
57.5°	73.8
60°	58.4
62.5°	44.6
65°	31.5
67.5°	20.7
70°	12.3
72.5°	5.4
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)