

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839603

Luminaire Tested: **LDS4C08D010 EU4089027 4LBSLI**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C08D010 EU4089027 4LBSLI
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 866.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839603

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839603

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75973
5°	74240
10°	69722
15°	64866
20°	60166
25°	54845
30°	48828
35°	43283
40°	38891
45°	34818
50°	29873
55°	24032
60°	17912
65°	11424
70°	5496
75°	902
80°	707
85°	0



TEST NUMBER: P839603

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	6.5
10°-20°	143.0	16.5
20°-30°	185.3	21.4
30°-40°	181.6	21.0
40°-50°	153.9	17.8
50°-60°	100.9	11.6
60°-70°	40.6	4.7
70°-80°	4.6	0.5
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	384.4	44.4
0°-40°	565.9	65.3
0°-60°	820.7	94.8
0°-90°	866.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	866.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	618	
5°	602	56
15°	510	143
25°	405	185
35°	289	182
45°	200	154
55°	112	101
65°	39	41
75°	2	5
85°	0	0
90°	0	



TEST NUMBER: P839603

CATALOG NUMBER: LDS4C08D010 EU4089027 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	618.4
2.5°	613.6
5°	602.0
7.5°	582.9
10°	558.9
12.5°	533.0
15°	510.0
17.5°	485.1
20°	460.2
22.5°	433.3
25°	404.6
27.5°	374.8
30°	344.2
32.5°	315.4
35°	288.6
37.5°	266.5
40°	242.5
42.5°	221.5
45°	200.4
47.5°	178.3
50°	156.3
52.5°	134.2
55°	112.2
57.5°	92.0
60°	72.9
62.5°	55.6
65°	39.3
67.5°	25.9
70°	15.3
72.5°	6.7
75°	1.9
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)