

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839606

Luminaire Tested: **LDS4C08D010 EU4089030 4LBCSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C08D010 EU4089030 4LBCSMB
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBCS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 608.0 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839606

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBCSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839606

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBCSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39215
5°	39081
10°	38660
15°	37991
20°	37143
25°	36152
30°	35011
35°	33655
40°	31963
45°	29067
50°	23986
55°	17671
60°	11990
65°	7035
70°	2766
75°	617
80°	849
85°	1410



TEST NUMBER: P839606

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBCSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.0	4.9
10°-20°	84.1	13.8
20°-30°	122.7	20.2
30°-40°	140.0	23.0
40°-50°	127.3	20.9
50°-60°	75.1	12.4
60°-70°	25.2	4.1
70°-80°	2.6	0.4
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	236.8	39.0
0°-40°	376.9	62.0
0°-60°	579.3	95.3
0°-90°	608.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	608.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	319	
5°	317	30
15°	299	84
25°	267	123
35°	224	140
45°	167	127
55°	82	75
65°	24	25
75°	1	3
85°	1	1
90°	0	



TEST NUMBER: P839606

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBCSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	319.2
2.5°	318.8
5°	316.9
7.5°	314.0
10°	309.9
12.5°	304.6
15°	298.7
17.5°	291.8
20°	284.1
22.5°	275.7
25°	266.7
27.5°	256.8
30°	246.8
32.5°	235.8
35°	224.4
37.5°	212.1
40°	199.3
42.5°	184.4
45°	167.3
47.5°	147.5
50°	125.5
52.5°	103.5
55°	82.5
57.5°	64.6
60°	48.8
62.5°	35.3
65°	24.2
67.5°	14.8
70°	7.7
72.5°	3.0
75°	1.3
77.5°	1.3
80°	1.2
82.5°	1.0
85°	1.0
87.5°	0.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)