

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839172

Luminaire Tested: **LD4C08D010 EU4089040 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P839172
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C08D010 EU4089040 4LBSLI
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 915.0 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839172

CATALOG NUMBER: LD4C08D010 EU4089040 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P839172

CATALOG NUMBER: LD4C08D010 EU4089040 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80260
5°	78446
10°	73664
15°	68541
20°	63565
25°	57949
30°	51594
35°	45728
40°	41104
45°	36781
50°	31555
55°	25381
60°	18919
65°	12064
70°	5819
75°	949
80°	707
85°	0



TEST NUMBER: P839172

CATALOG NUMBER: LD4C08D010 EU4089040 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.2	6.5
10°-20°	151.1	16.5
20°-30°	195.8	21.4
30°-40°	191.8	21.0
40°-50°	162.6	17.8
50°-60°	106.6	11.6
60°-70°	42.8	4.7
70°-80°	4.9	0.5
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	406.1	44.4
0°-40°	598.0	65.4
0°-60°	867.1	94.8
0°-90°	915.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	915.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	653	
5°	636	59
15°	539	151
25°	428	196
35°	305	192
45°	212	163
55°	118	107
65°	42	43
75°	2	5
85°	0	0
90°	0	



TEST NUMBER: P839172

CATALOG NUMBER: LD4C08D010 EU4089040 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	653.3
2.5°	648.3
5°	636.1
7.5°	615.8
10°	590.5
12.5°	563.2
15°	538.9
17.5°	512.6
20°	486.2
22.5°	457.9
25°	427.5
27.5°	396.0
30°	363.7
32.5°	333.3
35°	304.9
37.5°	281.6
40°	256.3
42.5°	234.0
45°	211.7
47.5°	188.4
50°	165.1
52.5°	141.8
55°	118.5
57.5°	97.2
60°	77.0
62.5°	58.7
65°	41.5
67.5°	27.3
70°	16.2
72.5°	7.1
75°	2.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)