

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839608

Luminaire Tested: **LDS4C08D010 EU4089030 4LBPSMB**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-18)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C08D010 EU4089030 4LBPSMB
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBPS TRIM WITH MB FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 690.0 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839608

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBPSMB

Luminous Intensity Polar Plot





TEST NUMBER: P839608

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBPSMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90			90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70			70
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	62			62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55			55
6	77	65	58	52	75	65	57	52	63	56	52	61	56	51	60	55	51	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	47	42	66	54	47	42	53	47	42	52	46	42	51	46	41	40			40
9	63	51	43	38	62	50	43	38	49	43	38	48	42	38	47	42	38	36			36
10	59	47	40	35	58	47	40	35	46	39	35	45	39	35	44	39	35	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44510
5°	44359
10°	43874
15°	43116
20°	42150
25°	41019
30°	39735
35°	38199
40°	36277
45°	32976
50°	27235
55°	20048
60°	13612
65°	7965
70°	3161
75°	712
80°	920
85°	1551



TEST NUMBER: P839608

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBPSMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.1	4.9
10°-20°	95.5	13.8
20°-30°	139.2	20.2
30°-40°	158.9	23.0
40°-50°	144.5	20.9
50°-60°	85.2	12.4
60°-70°	28.6	4.1
70°-80°	3.0	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.8	39.0
0°-40°	427.7	62.0
0°-60°	657.4	95.3
0°-90°	690.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	690.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	362	
5°	360	34
15°	339	95
25°	303	139
35°	255	159
45°	190	144
55°	94	85
65°	27	29
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P839608

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBPSMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	362.3
2.5°	361.7
5°	359.7
7.5°	356.3
10°	351.7
12.5°	345.7
15°	339.0
17.5°	331.2
20°	322.4
22.5°	312.9
25°	302.6
27.5°	291.4
30°	280.1
32.5°	267.6
35°	254.7
37.5°	240.7
40°	226.2
42.5°	209.2
45°	189.8
47.5°	167.4
50°	142.5
52.5°	117.5
55°	93.6
57.5°	73.3
60°	55.4
62.5°	40.1
65°	27.4
67.5°	16.8
70°	8.8
72.5°	3.4
75°	1.5
77.5°	1.5
80°	1.3
82.5°	1.1
85°	1.1
87.5°	0.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)