

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839614

Luminaire Tested: **LDS4C08D010 EU4089030 4LBSWH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C08D010 EU4089030 4LBSWH
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LBS TRIM WITH WH FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 803.0 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839614

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBSWH

Luminous Intensity Polar Plot





TEST NUMBER: P839614

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBSWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51598
5°	51352
10°	50299
15°	48471
20°	46242
25°	43743
30°	41267
35°	38844
40°	36581
45°	34105
50°	31096
55°	27459
60°	23244
65°	18256
70°	13039
75°	7120
80°	1273
85°	0



TEST NUMBER: P839614

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBSWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	4.9
10°-20°	106.9	13.3
20°-30°	148.5	18.5
30°-40°	162.0	20.2
40°-50°	151.2	18.8
50°-60°	114.7	14.3
60°-70°	62.8	7.8
70°-80°	17.3	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	294.7	36.7
0°-40°	456.8	56.9
0°-60°	722.7	90.0
0°-90°	803.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	420	
5°	416	39
15°	381	107
25°	323	148
35°	259	162
45°	196	151
55°	128	115
65°	63	63
75°	15	17
85°	0	0
90°	0	



TEST NUMBER: P839614

CATALOG NUMBER: LDS4C08D010 EU4089030 4LBSWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	420.0
2.5°	420.0
5°	416.4
7.5°	411.1
10°	403.2
12.5°	392.6
15°	381.1
17.5°	366.9
20°	353.7
22.5°	337.7
25°	322.7
27.5°	307.7
30°	290.9
32.5°	275.0
35°	259.0
37.5°	243.1
40°	228.1
42.5°	212.2
45°	196.3
47.5°	180.4
50°	162.7
52.5°	145.9
55°	128.2
57.5°	111.4
60°	94.6
62.5°	77.8
65°	62.8
67.5°	48.6
70°	36.3
72.5°	24.8
75°	15.0
77.5°	7.1
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)