

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839179

Luminaire Tested: **LD4C100D010 EU41009030 4LBPSMW**

Issue Date: 6/29/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P839179  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/29/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C100D010 EU41009030 4LBPSMW  
Description: 4 INCH 10000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBPS TRIM WITH MW FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9943.0 lumens  
Efficiency: N/A  
Efficacy: 86.9 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.29  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 114.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839179

CATALOG NUMBER: LD4C100D010 EU41009030 4LBPSMW

### Luminous Intensity Polar Plot





TEST NUMBER: P839179

CATALOG NUMBER: LD4C100D010 EU41009030 4LBPSMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	85	100	93	88	84	90	86	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66			66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58			58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51			51
6	75	63	55	49	73	62	54	49	60	53	48	59	52	48	57	52	47	46			46
7	70	57	49	44	68	57	49	43	55	48	43	54	47	43	52	47	43	41			41
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37			37
9	61	48	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	33			33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	42	36	32	30			30

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	572890
5°	571959
10°	568842
15°	562257
20°	552054
25°	540087
30°	527233
35°	512199
40°	491578
45°	456001
50°	392841
55°	313358
60°	243962
65°	182615
70°	132509
75°	105092
80°	98411
85°	98107



TEST NUMBER: P839179

CATALOG NUMBER: LD4C100D010 EU41009030 4LBPSMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	440.3	4.4
10°-20°	1245.0	12.5
20°-30°	1834.7	18.5
30°-40°	2131.3	21.4
40°-50°	2003.4	20.1
50°-60°	1326.1	13.3
60°-70°	639.0	6.4
70°-80°	246.4	2.5
80°-90°	76.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3519.9	35.4
0°-40°	5651.2	56.8
0°-60°	8980.7	90.3
0°-90°	9943.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9943.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4663	
5°	4638	440
15°	4421	1245
25°	3984	1835
35°	3415	2131
45°	2625	2003
55°	1463	1326
65°	628	639
75°	221	246
85°	70	77
90°	0	



TEST NUMBER: P839179

CATALOG NUMBER: LD4C100D010 EU41009030 4LBPSMW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4663.2
2.5°	4658.9
5°	4637.9
7.5°	4606.2
10°	4559.9
12.5°	4496.6
15°	4420.7
17.5°	4328.0
20°	4222.6
22.5°	4106.6
25°	3984.3
27.5°	3853.6
30°	3716.6
32.5°	3571.2
35°	3415.2
37.5°	3244.4
40°	3065.2
42.5°	2862.8
45°	2624.6
47.5°	2354.8
50°	2055.4
52.5°	1751.8
55°	1463.0
57.5°	1214.3
60°	992.9
62.5°	794.8
65°	628.2
67.5°	487.0
70°	368.9
72.5°	280.4
75°	221.4
77.5°	179.2
80°	139.1
82.5°	103.3
85°	69.6
87.5°	40.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)