

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839195

Luminaire Tested: **LD4C10D010 EU4109030 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P839195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C10D010 EU4109030 4LBSH
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 990.0 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.8
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839195

CATALOG NUMBER: LD4C10D010 EU4109030 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839195

CATALOG NUMBER: LD4C10D010 EU4109030 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63614
5°	63314
10°	62013
15°	59753
20°	57002
25°	53937
30°	50871
35°	47902
40°	45097
45°	42045
50°	38340
55°	33863
60°	28649
65°	22500
70°	16056
75°	8781
80°	1556
85°	0



TEST NUMBER: P839195

CATALOG NUMBER: LD4C10D010 EU4109030 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	4.9
10°-20°	131.8	13.3
20°-30°	183.1	18.5
30°-40°	199.8	20.2
40°-50°	186.4	18.8
50°-60°	141.4	14.3
60°-70°	77.4	7.8
70°-80°	21.3	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	363.4	36.7
0°-40°	563.2	56.9
0°-60°	890.9	90.0
0°-90°	990.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	990.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	518	
5°	513	49
15°	470	132
25°	398	183
35°	319	200
45°	242	186
55°	158	141
65°	77	77
75°	18	21
85°	0	0
90°	0	



TEST NUMBER: P839195

CATALOG NUMBER: LD4C10D010 EU4109030 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	517.8
2.5°	517.8
5°	513.4
7.5°	506.9
10°	497.1
12.5°	484.0
15°	469.8
17.5°	452.4
20°	436.0
22.5°	416.4
25°	397.9
27.5°	379.3
30°	358.6
32.5°	339.0
35°	319.4
37.5°	299.8
40°	281.2
42.5°	261.6
45°	242.0
47.5°	222.4
50°	200.6
52.5°	179.8
55°	158.1
57.5°	137.3
60°	116.6
62.5°	95.9
65°	77.4
67.5°	59.9
70°	44.7
72.5°	30.5
75°	18.5
77.5°	8.7
80°	2.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)