

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839198

Luminaire Tested: **LD4C10D010 EU4109035 4LBSH**

Issue Date: 2/14/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P839198  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C10D010 EU4109035 4LBSH  
Description: 4 INCH 1000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1004.0 lumens  
Efficiency: N/A  
Efficacy: 102.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.8  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P839198

CATALOG NUMBER: LD4C10D010 EU4109035 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P839198

CATALOG NUMBER: LD4C10D010 EU4109035 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	64510
5°	64214
10°	62886
15°	60605
20°	57812
25°	54696
30°	51594
35°	48577
40°	45739
45°	42636
50°	38875
55°	34334
60°	29067
65°	22820
70°	16272
75°	8924
80°	1556
85°	0



TEST NUMBER: P839198

CATALOG NUMBER: LD4C10D010 EU4109035 4LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.2	4.9
10°-20°	133.7	13.3
20°-30°	185.7	18.5
30°-40°	202.6	20.2
40°-50°	189.0	18.8
50°-60°	143.5	14.3
60°-70°	78.6	7.8
70°-80°	21.6	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	368.5	36.7
0°-40°	571.1	56.9
0°-60°	903.6	90.0
0°-90°	1004.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1004.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	525	
5°	521	49
15°	476	134
25°	404	186
35°	324	203
45°	245	189
55°	160	143
65°	78	79
75°	19	22
85°	0	0
90°	0	



TEST NUMBER: P839198

CATALOG NUMBER: LD4C10D010 EU4109035 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	525.1
2.5°	525.1
5°	520.7
7.5°	514.1
10°	504.1
12.5°	490.8
15°	476.5
17.5°	458.8
20°	442.2
22.5°	422.3
25°	403.5
27.5°	384.7
30°	363.7
32.5°	343.8
35°	323.9
37.5°	304.0
40°	285.2
42.5°	265.3
45°	245.4
47.5°	225.5
50°	203.4
52.5°	182.4
55°	160.3
57.5°	139.3
60°	118.3
62.5°	97.3
65°	78.5
67.5°	60.8
70°	45.3
72.5°	31.0
75°	18.8
77.5°	8.8
80°	2.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)