

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P839622

Luminaire Tested: **LDS4C08D010 EU4089035 4LBSH**

Issue Date: 8/24/2022



Test Information

Test Method: LM-79-08
Report Number: P839622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 8/24/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDS4C08D010 EU4089035 4LBSH
Description: 4 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 876.0 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P839622

CATALOG NUMBER: LDS4C08D010 EU4089035 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P839622

CATALOG NUMBER: LDS4C08D010 EU4089035 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77		
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67		
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51		
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41		
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37		
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34		
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	56279
5°	56026
10°	54864
15°	52872
20°	50439
25°	47715
30°	45012
35°	42383
40°	39901
45°	37198
50°	33925
55°	29965
60°	25357
65°	19913
70°	14224
75°	7785
80°	1344
85°	0



TEST NUMBER: P839622

CATALOG NUMBER: LDS4C08D010 EU4089035 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.9	4.9
10°-20°	116.6	13.3
20°-30°	162.0	18.5
30°-40°	176.8	20.2
40°-50°	164.9	18.8
50°-60°	125.2	14.3
60°-70°	68.5	7.8
70°-80°	18.9	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	321.5	36.7
0°-40°	498.3	56.9
0°-60°	788.3	90.0
0°-90°	876.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	876.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	458	
5°	454	43
15°	416	117
25°	352	162
35°	283	177
45°	214	165
55°	140	125
65°	68	69
75°	16	19
85°	0	0
90°	0	



TEST NUMBER: P839622

CATALOG NUMBER: LDS4C08D010 EU4089035 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	458.1
2.5°	458.1
5°	454.3
7.5°	448.5
10°	439.8
12.5°	428.3
15°	415.7
17.5°	400.3
20°	385.8
22.5°	368.4
25°	352.0
27.5°	335.7
30°	317.3
32.5°	300.0
35°	282.6
37.5°	265.2
40°	248.8
42.5°	231.5
45°	214.1
47.5°	196.8
50°	177.5
52.5°	159.1
55°	139.9
57.5°	121.5
60°	103.2
62.5°	84.9
65°	68.5
67.5°	53.0
70°	39.6
72.5°	27.0
75°	16.4
77.5°	7.7
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)